

IEC STANDARD BURDEN SETS (CURRENT)

FUNCTIONALITY

Testing and calibrating current transformers often requires standard burdens of reliable accuracy and stability, and burdens that are immune to stray fields and harmonics. The burden sets have been carefully designed to meet these requirements. They also provide the standard burdens required for the testing of current transformers for metering service, and for the testing (within the current rating provided by the sets) of current transformers for relaying applications, all as called for by IEC (International Electrotechnical Commission) Publication 185: 1987.

The burden sets are of the portable type, supplied in black metal housings with engraved bakelite panels. Extensive design and development work in perfecting these burden sets, and the quality material and skillful workmanship employed assure excellent performance and quality throughout.



SPECIFICATIONS

- Accuracy: Resistance and inductance within 1.0%
- Stability: At the rated frequency, the variation with current of the impedance and power factor of these current transformer burdens does not exceed 2.0% in the range from 10% to 50% of rated current and 1.0% from 50% to 200% of rated current. This includes the effects of self-heating in an ambient temperature ranging from 60 degrees F. to 80 degrees F.
- Dimensions and weights: Check chart on next page.



IEC STANDARD BURDEN SETS (CURRENT)

A TESCO COMPANY

Burden	IEC	Volt-	Power	Length	Width	Height	Weight
Туре	Designation	Amperes	Factor	(in.)	(in.)	(in.)	(lbs.)
BSC-32†	2.5	2.5	1.0	19.50	11.50	12.125	69
	5	5.0	8.0				
	7.5	7.5	0.8				
	10	10	8.0				
	15	15	8.0				
	30	30	0.8				
BSC-33*	2.5	2.5	1.0	19.50	11.50	6.00	34
	5	5.0	8.0				
	7.5	7.5	8.0				
	10	10	8.0				
	15	15	8.0				
	30	30	0.8				
BSC-35‡	2.5	2.5	1.0	19.50	11.50	12.125	69
	5	5.0	8.0				
	7.5	7.5	8.0				
	10	10	8.0				
	15	15	8.0				
	30	30	0.8				
BSC-36#	2.5	2.5	1.0	19.50	11.50	6.00	34
	5	5.0	8.0				
	7.5	7.5	8.0				
	10	10	8.0				
	15	15	8.0				
	30	30	0.8				

[†] Values are for 50 Hz. and 1 Ampere.

Leads: Leads are not supplied with the burden sets. All the current transformer burden sets are adjusted for a 5 ft. pair of #8 closely spaced copper conductors. For the best accuracy it is important to use equivalent leads.

^{*} Values are for 50 Hz. and 5 Amperes.

[‡] Values are for 60 Hz. and 1 Ampere.

[#] Values are for 60 Hz. and 5 Amperes.